# Revelation III

The Revelation III professional-grade microscope is a best-seller into physician and veterinarian clinics, as well as universities and medical schools. New for 2013, the Revelation III now comes with LED illumination, for daylight color, low heat, low power consumption, and super-long bulb life (30,000). Equipped for performance, its features include titanium-finished DIN achromatic or DIN Plan optics and a 30-year anti-fungal coating. The Revelation III is the choice for superior performance at a great value!

# CE

### HEAD

Binocular (Seidentopf)
Inclined 30°, rotates 360°
Diopter adjustment
10X/18 wide field eyepieces (10X/20HP available)
Monocular, trinocular, dual binocular and
45° sliding heads available
Interpupillary distance range:
Binoc head: 48-75mm
Trinoc head: 55-75mm

### NOSEPIECE

Quadruple forward-facing nosepiece Multiple ball bearing mounted

### **OBJECTIVES**

DIN Achromatic or DIN Plan 30 year anti-fungal coating 4X, 10X, 40X, 100XR (oil) Parfocal, parcentric, color-coded

### STAGE

Mechanical stage (140mm x 140mm) Coaxial drive controls Range of traverse is 73mm x 43mm Stage locking lever Slow-close hydraulic slide finger

### FOCUS

Coarse adjustment: range of 30mm Fine adjustment: graduation of 2µm Tension control knob

## ILLUMINATION

Moveable Abbe condenser, NA 1.25, rack & pinion lris diaphragm 100-240V AC / 50-60Hz Auto-Switching Input Light Options:

Variable halogen light source (12V/20W bulb) - Optional Variable LED light source (3W bulb) - Standard

### Revelation III

Model # Description

R3M-BN4A-DAL3 Binoc head, 4-10-40-100 DIN Achromatic objectives, LED illumination

R3M-TN4A-DAL3 Trinoc head, 4-10-40-100 DIN Achromatic objectives, LED illumination

R3M-BN4A-DPL3 Binoc head, 4-10-40-100 DIN Plan objectives, LED illumination

R3M-TN4A-DPL3 Trinoc head, 4-10-40-100 DIN Plan objectives, LED illumination

R3M-MN4A-DAL3 Monoc head, 4-10-40-100 DIN Achromatic objectives, LED illumination

- •Medical-Grade Microscope
- Anti-Fungal Coating on All Lenses
- •Field-Ready Portable Options

### **WEIGHT AND DIMS**

Height: 15" (380mm) Length: 9" (230mm) Width: 7" (178mm) Weight: 14 lbs. (6.4kg)



P 770.270.1394 F 770.270.2389

865 Marathon Parkway Lawrenceville GA 30046

LWScientific.com