



Presto!

FOOD PREPARATION



SLICERS



PS-10



PS-12



PS-12D (Deluxe)

STANDARD FEATURES

Reliable and dependable
belt drive design

•
Easy to operate

•
Removable carriage
for easy maintenance

•
Adjustable slicing knob

•
Built in sharpener

•
Ring guard

•
Compact, space saving design
for limited counter space

•
Permanent lubricated carriage ball
bearings to ensure quiet operation

•
Manufactured in anodized aluminum,
resisting corrosion by salts and acids

Warranty:

One year carry-in
parts and labor



MIXERS

STANDARD FEATURES

- Reliable and dependable gear drive design
-
- Long life gear box
-
- 3 speeds
-
- Silent operation
-
- Heat-treated hardened alloy steel gears and shaft
-
- Stainless steel bowl safety guard
-
- Side mounted controls.
Separate start and emergency stop button
-
- Highest quality aluminum alloy used for maximum standards of hygiene
-
- Safety interlock switch prevents operation when either bowl is lowered or guard is opened
-
- 6 foot cord and plug



PM-10



PM-20

STANDARD ACCESSORIES

Mixer accessories include
S/Steel Bowl,
S/Steel Wire Whip,
Aluminum Flat Beater,
and Aluminum Dough Hook.

Warranty:
2 years parts and 1 year labor,
exclusive of wear items



MEAT SLICERS / SPECIFICATIONS

Model	Blade Size	Motor	Electrical	Transmission	RPM	Ship Weight	Freight Class
PS-10	10"	.25 HP	120V /60 / 1	Belt drive	300	45 Lbs	85
PS-12	12"	.33 HP	120V /60 / 1	Belt drive	300	57 Lbs	85
PS-12D	12"	.50 HP	120V /60 / 1	Belt drive	300	75 Lbs	85

MIXERS / SPECIFICATIONS

Model	Capacity	Flour Capacity	Motor	Electrical	Transmission	Ship Weight	Freight Class	Dimensions
PM-10	10 QT.	3.3 lbs (1.5 kg)	.5 HP	120V/60/1	Gear drive	196 Lbs	85	15"x13"x30"
PM-20	20 QT.	6.6 lbs (3 kg)	1.0 HP	120V/60/1	Gear drive	280 Lbs	85	21"x16.5"x30.5"



MVP GROUP CORPORATION

5659 Royalmount Ave. | Montreal | QC, Canada | H4P 2P9
 Tel: 514.737.9701 / 888.275.4538 | Fax: 514.342.3854 / 877.453.8832
www.mvpgroupcorp.com | sales@mvpgroupcorp.com



In line with our continuing policy on research and product development, we reserve the right to alter specifications and prices without notice.