

# 130° CAMERA WITH 18 INFRA-RED ILLUMINATORS (RCA CONNECTORS)

## RVS-771



## SPECIFICATIONS

CAMERA	1/4 SHARP COLOR CCD
PICTURE ELEMENTS	250,000 PIXELS
GAMMA CORRECTION	R=0.45 TO 1.0
IMAGE SENSOR	480TV LINES PAL:500(H)*582(V), NTSC:510(H)*492(V)
LENS	2.1MM
VIEW ANGLE	130°
SYNC SYSTEM	INTERNAL SYNCHRONIZATION
INFRA-RED DISTANCE	50 FEET (18 INFRARED IR)
USABLE ILLUMINATION	0 LUX (IR ON)
POWER SOURCE	DC 12V (+/- 10%)
S/N RATIO	MORE THAN 48DB
ELECTRONIC IRIS	1/50, 1/60-1/100,000SEC
VIDEO OUTPUT	1V.P.P 750HM
IR SWITCH CONTROL	CDS AUTOMATIC CONTROL
VIBRATION AND SHOCK RATING	20G / 100G
OPERATING TEMPERATURE	-25°C - 50°C / RH 95% MAX
STORAGE TEMPERATURE	-25°C - 60°C / RH 95% MAX

REAR VIEW  
**SAFETY**  
REVERSE WITH CONFIDENCE™