



# SBC677BI



34.5" x 23.63" x 25.75" (H x W x D)

Built-in undercounter frost-free beer dispenser with stainless steel wrapped door, digital thermostat, and complete tap kit

### Highlights:

Frost-free operation ensures minimum user maintenance

Flexible design allows built-in or freestanding use in 24" spaces

Complete tap kit includes everything you need for the perfect pour

"Cold pipe" tapping system helps to reduce foam

### Product Features:

Full-sized beer dispenser	Large interior can accept a full half barrel keg
Built-in capable	Front-breathing design allows fully recessed installation under counters
Frost-free operation	No-frost operation for minimum user maintenance
Stainless steel door	Fully wrapped 304 grade stainless steel door offers lasting durability and style
Professional horizontal handle	Sleek stainless steel handle is mounted horizontally for a modern look
Digital thermostat	Electronic controls ensure easy temperature management for optimum beer storage
Complete tap kit	Includes a 5 lb. CO2 tank and regulator, draft arm, dual Sankey American tap, connection hardware, and cleaning kit
Chilled tap system	Unique "cold pipe" addition ensures beer stays cold inside the tap tower, reducing the amount of foam keeping every pour at its best
Stainless steel drip tray	Two-piece drip tray included to help catch spills



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com



www.summitappliance.com



## SBC677BI Specifications:

Overview	
Height	34.5"
Width	23.63"
Depth	25.75"
Depth with Handle	27.25"
Depth with door at 90°	48.25"
Capacity	6.5 cu.ft.
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	308.0kWh/year
Amps	1.1
Voltage/Frequency	115 V AC/60 Hz
Weight	106.0 lbs.
Shipping Weight	120.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Beer Dispenser	
Door Swing	RHD
Reversible	Yes
Tap Kit	Yes
Height with Tap	50.0"
Number of Taps	1
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	2
Thermostat Type	Digital
Interior Light	Yes
Fan Type	Interior and Exterior
Refrigerant	R600a
Refrigerant Amount	1.2 oz.
High Side PSI	277.0
Low Side PSI	103.0
Inter Height	27.75"
Interior Width	19.25"
Interior Depth	24.25"

Compressor Step Height	6.25"
Compressor Step Width	19.25"
Compressor Step Depth	9.75"
Wheel Qty	4
Surface	Stainless Steel
Temperature Range	32° to 50°F



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com www.summitappliance.com