



TW30B

30" Oscillating Circulation Fan



Air Velocity (@ 10') :	1100
Blade Color :	Metallic
Blade Material :	Aluminum
CFM (free air) :	9600
CFM (high) :	9600
CFM (low) :	8500
CFM Calculation Standard :	ANSI/AMCA Standard 230-99
CFM Range (Free Air) :	10001 - 15000
CFM/Watt (free Air) :	20.3
Component Certifications :	Motor - CSA
Cord :	Included - Wired
Cord Length (feet) :	10
Country of Origin :	US
Diameter (inches) :	30
Drive Type :	Direct
Fixed or Portable :	Fixed
Frequency (Hz) :	60
Guard Color :	Black

Guard Material & Coating :	Powder Coated Steel
Guard Spacing (inches) :	1/2 OSHA
Mount Type Recommended :	WMTA30-B, VS30FMT
Nameplate Amps :	5.9
Number of Wings :	3
Oscillating :	Yes
Schaefer Performance Test No. :	702
Phase :	1
Power (hp) :	1/2
Power (Voltage & Phase) :	115 Single Phase
Product Color :	Black
Product Weight (pounds) :	62
Sound Level (dBA @ 10') :	71
Speed Control Compatible :	No
Speeds :	2
Switch :	On product
VFD Compatible :	No
Voltage :	115