



VK12

12" Versa-Kool Circulation Fan



Air Velocity (@ 5 times diameter) :	680	Guard Spacing (inches) :	1/2 - 1 UL507
BESS Lab Performance Test No. :	12370	Housing Color :	White
Blade Color :	Metallic	Max RPM :	1725
Blade Material :	Aluminum	Mount Included :	VS12FMT
CFM (free air) :	1470	Mount Type Included :	Ceiling
CFM Calculation Standard :	ANSI/AMCA Standard 230-99	Nameplate Amps :	1.3/.65
CFM Range (Free Air) :	1001 - 2500	Number of Wings :	3
CFM/Watt (free Air) :	14	Oscillating :	No
Component Certifications :	Motor - UL/CSA	Phase :	1
Cord :	Included - Not Wired	Power (hp) :	1/10
Cord Length (feet) :	5	Power (Voltage & Phase) :	115/230 Single Phase
Country of Origin :	US	Product Color :	White
Diameter (inches) :	12	Product Weight (pounds) :	18
Drive Type :	Direct	Speed Control Compatible :	Yes
Fixed or Portable :	Fixed	Speeds :	1
Frequency (Hz) :	60	Switch :	Not included
Guard Color :	White	VFD Compatible :	No
Guard Material & Coating :	Powder Coated Steel	Voltage :	115/230

