

SCR7012DB



34.13" x 35.5" x 19.63" (H x W x D)

Commercial back bar beverage center for freestanding use, with self-closing French doors; replaces SCR7012D

Highlights:

Less than 20" deep for an easy fit behind the bar

Commercially approved for use in foodservice establishments

Two self-closing glass doors offer a full view of contents inside

Product Features:

Automatic defrost	Reduced maintenance with auto defrost system
Commercially approved	ETL-S Approved to ANSI-NSF Standard 7 for use in commercial establishments
Two glass doors	Solid glass doors provide a clear view of interior contents
Two factory installed locks	Protect contents in both sections with a key lock on each door
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Digital thermostat	Electronic controls located in the front kickplate for easy temperature management
Interior light	Illuminates the interior for a an attractive view of stored contents
Stainless steel trim on doors	Added touch of elegance with a stainless steel door trim
Fully finished textured black cabinet	Allows the unit to be used freestanding

SCR7012DB Specifications:

Overview

Height of Cabinet	34.13" (87 cm)
Width	35.5" (90 cm)
Depth	19.63" (50 cm)
Depth with Handle	21.13" (54 cm)
Depth with door at 90°	36.0" (91 cm)
Capacity	7.4 cu.ft. (210 L)
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.2
Voltage/Frequency	115 V AC/60 Hz
Weight	150.0 lbs. (68 kg)
Shipping Weight	200.0 lbs. (91 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years

Refrigerator Features

Door Swing	French
Shelf Type	Chrome
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	1.92oz.
High Side PSI	215.0
Low Side PSI	60.0
Interior Light	Yes

Dimensions

Interior Height	28.25" (72 cm)
Interior Width	32.5" (83 cm)
Interior Depth	15.0" (38 cm)
Compressor Step Height	7.5" (19 cm)
Compressor Step Width	32.5" (83 cm)
Compressor Step Depth	7.25" (18 cm)

