

PHC51G



29.5" x 23.38" x 19.88" (H x W x D)

Single chamber compact warming cabinet with glass door, digital thermostat, and lock

Highlights:

Compact size makes it ideal for use on top of counters

Digital controls conveniently located for easy adjustment and temperature viewing

Factory installed lock allows you to restrict access to staff

Designed and constructed in the USA

Product Features:

Compact size	Small footprint is ideal for countertop placement
Digital thermostat	Electronic controls are conveniently located for easy temperature adjustment
Electronic readout	Large LED temperature display ensures your staff can easily monitor the interior temperature
120 to 150°F Temperature Range	Designed and set for hospital blankets
Double pane tempered glass door	Heat-safe glass door offers a full view of stored contents
Self-closing door	Door is equipped with self-closing mechanism and magnetic gaskets to prevent heat loss
Factory installed lock	Keyed lock for a secure interior
Hammered aluminum interior	Ensures easy cleaning inside
Flush back	Space saving design with easier cleanability

PHC51G Specifications:

Overview		
Height		29.5"
Width		23.38"
Depth		19.88"
Depth with door at 90°		42.0"
Capacity		2.0 cu.ft.
Door		Glass
Cabinet		Gray
US Electrical Safety		ETL
Canadian Electrical Safety		ETL-C
Amps		5.5
Voltage/Frequency	115 V AC/60 Hz	
Weight		140.0 lbs.
Shipping Weight		160.0 lbs.
Parts & Labor Warranty		1 Year
Warming Cabinet		
Door Swing		RHD
Reversible		No
Shelf Type		Wire
Shelf Qty		1
Thermostat Type		Digital
Interior Height		18.0"
Interior Width		18.75"
Interior Depth		15.38"
Temperature Range	120 to 150°F	

