



OPTIONAL FLANGE

MODEL	A	B	C	APPROX. WEIGHT
WS-12	12	12	15	5
WS-16	16	16	19	7
WS-18	18	18	21	8
WS-20	20	20	23	9
WS-24	24	24	27	12
WS-30	30	30	33	15
WS-36	36	36	39	23
WS-42	42	42	45	29
WS-48	48	48	51	35
WS-54	54	54	57	48
WS-60	60	60	63	50

STANDARD FLANGE

NOTES

1. FRAME AND BLADES ARE CORROSION RESISTANT EXTRUDED ALUMINUM.
2. FELT EDGES ON BLADES.
3. ALSO AVAILABLE WITH MANUAL CHAIN OPERATOR OR MOTOR OPERATED.
4. FOR VERTICAL MOUNT, HORIZONTAL AIR FLOW ONLY.
5. MAXIMUM FACE VELOCITY: 2500 FPM.
6. MAXIMUM TEMPERATURE: 200°F. WITHOUT ELECTRIC MOTOR 130°F. WITH ELECTRIC MOTOR
7. MAXIMUM DIFFERENTIAL PRESSURE: 1" WG.
8. WS-12 THROUGH WS-30 ARE SINGLE PANEL; WS 36 THROUGH WS-60 ARE DOUBLE PANEL

WS AUTOMATIC SHUTTER

AMERICRAFT MANUFACTURING CO

P.O. Box 1108  
Mason, Ohio 45040-1108

AMC NO.

Cust NO.

Project

Notes

SEE DRAWING

Drawn by  
**A. Plaza**

Page Number  
1 of 1

Certified by

Revision  
A

File  
Backdraft  
damper

Scale  
Not to scale

Date  
08/31/10