Product information presented here reflects conditions at time of publication. Consult factory regarding discrepancies or inconsistencies.





SECTION: 2.10.030 FM2058

> 0610 Supersedes 0909

visit our web site: www.zoeller.com

SHIP TO: 3649 Cane Run Road • Louisville, KY 40211-1961 (502) 778-2731 • 1 (800) 928-PUMP • FAX (502) 774-3624

COMPARE THESE FEATURES

- 115 Volts single phase/60 Hz
- Self-priming 7 feet or less above liquid source
- Lifts water from 15 feet below pumping level
- Garden hose connections
- Use to remove water from:
 - ✓ waterbeds
 - ✓ washing machines
 - ✓ water heaters
- Use to add propylene glycol antifreeze to radiant heating lines
- Maximum temperature for dewatering-130°F (54°C)
- 90 days limited warranty

Model 311

- Transfers up to 337 gallons per hour
- Includes extra impeller, gasket and one 6 ft. hose with strainer
- 6 ft. power cord

Model	Voltage	Max. Flow	Shut-off
Number		1' Head	Head
311-0002	115VAC	337 GPH	39'

Replacement Impeller/Gasket Kit P/N 015391

Model 311

"MIGHTY MOVER"

PORTABLE NON-SUBMERSIBLE UTILITY PUMP

FOR DEWATERING



Model 311



Tested to UL Standard UL778 and Certified to CSA Standard C22.2 No. 108

Product may not be exactly as pictured.

COMPARE THESE FEATURES

- · Cast Iron pump housing for long life
- Engineered Thermo Plastic Impeller designed for durability
- 115V, 1/2 HP motor
- · Use for removing water from water heaters, power washing, water transfer and adding propylene glycol anti-freeze to radiant heating lines
- · Handle on prime plug allows for easy priming - no tools required
- · Permanently lubricated ball bearings
- Carbon ceramic shaft seal
- · 20 ft. power cord
- On/Off switch on motor housing
- Includes 3/4" NPT brass, lead free garden hose adapters, suction screen and extra set of brushes
- Maximum temperature for dewatering-120°F (49°C).
- One-year limited warranty



Model 314

The "High Capacity" **Water Mover**

PORTABLE NON-SUBMERSIBLE UTILITY PUMP **FOR DEWATERING**





