

S19-2000, S19-2000EFX Emergency Fixture Thermostatic Mixing Valves

- Exceeds ANSI Z358.1
- · ASSE 1071 Certified
- Reliable Liquid-Filled Thermostat with 10-Year Warranty
- · Checkstops on Inlets
- Adjustable Set Point within Temperature Range
- Accurate Temperature Control to within ±3° F
- Built-in Cold Water Bypass, Assuring Cold Flow
- Positive Shutoff of Hot Supply When Cold Supply is Lost
- · Easy Installation and Serviceability
- Dirt and Lime Resistant
- Dial Thermometer
- · Factory Assembled and Tested
- · Universal Mounting Capability
- · Cabinet Features:
 - 18 Gauge Body & Door
 - Left-Hand Hinge
 - Cylinder Lock
 - Inlet/Outlet Knock-Out Holes for Mounting Flexibility
 - Stainless Steel or Baked White Enamel Finishes
 - Surface-Mounted or Recessed Style with Flange

Valve Specifications

Maximum Operating Pressure

125 PSI (860 kPA)

Maximum Inlet Temperature

180° F (82° C)

Recommended Inlet Temperature

120° F (49° C) – 140° F (60° C)


Tempera	ture Range	Set Point		
Std.	65° F (18° C) to 90° F (32° C)	85° F (29° C)		

Flow Capacities - GPM (L/Min)

	Min	Pressure Drop – PSI (Bar)						
Model	Min.	5	10	15	20	30	45	60
	Flow	(.5)	(1.0)	(1.5)	(2.0)	(2.5)	(3.0)	(4.0)
\$19-2000	1.5	3.0	4.0	5.0	6.0	7.3	9.0	10.5
	(5.5)	(13.5)	(19.0)	(23.5)	(27.0)	(30.5)	(33.5)	(38.5)
Cold Bypass Only		2.3	3.2	4.0	4.6	5.6	6.8	7.7
		(10.5)	(14.5)	(18.0)	(21.0)	(23.5)	(25.5)	(29.5)



This plumbing fixture is not intended to dispense water for human consumption through drinking or for preparation of food or beverages.



Optional Selections				
Finish □ C	Chrome Plated			
Bracket □ B	Wall Mounting Bracket			
Cabinets				
□ SS	Surface Mount Stainless Steel			
□ RS	Recessed Stainless Steel			
□ SE	Surface Mount White Enamel			
□ RE	Recessed White Enamel			
□W	Plexi-glass Window in Door			

Code Compliance and Certifications

ASSE 1071 & UPC certified.





Engineer's Approval_

Page 1 of 3 4/25/2014
This information is subject to change without notice.
Bradley_TMV_Emergency_EFX8


© 2015 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com




Dimensions (mm)

Side


View






Dimensions — S19-2000 Recessed Cabinet





Side View




Page 2 of 3 4/25/2014
This information is subject to change without notice.
Bradley_TMV_Emergency_EFX8

© 2015 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com


Dimensions — S19-2000 Surface-Mounted Cabinet


(mm)

Front View



Side View





Bottom View Is the Same for Both Surface-Mounted and Recessed Dimensions.

Recessed View

11" (279)

Surface-Mounted & Recessed

Page 3 of 3 4/25/2014
This information is subject to change without notice.
Bradley_TMV_Emergency_EFX8

© 2015 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com