KENDALL HOWARD

PHANTOM CLASS® OPEN FRAME SWING-OUT RACK





The Phantom Class[®] Open Frame Swing-Out Rack is truly in a class of its own. The unrivaled quality allows you to install rack mount equipment up off the floor, and it can easily support upwards of 150 lbs. The 90 degree swing-out provides installers the access they need to install and manage patch panels, routers, hubs, switches, cabling, and other networking devices.

FEATURES

90 Degree Swing-Out - Pivoting rack mount frame swings out 90 degrees to easily access the rear of installed network equipment. Integrated positive stop prevents the gate from being opened more than 90 degrees to avoid causing damage or stress to cabling and connection points. A simple latching mechanism securely holds the swing gate in the closed position when finished.

Easy to Assemble - Knockdown design reduces shipping charges and assembles in a snap. With just a few steps the rack is easy to assemble, and with the 16" on center mounting holes you can mount directly to your wall studs.

Numerous Cable Lacing Points - Both the front and rear of the wall rack feature oblong cutouts for securing cable bundles. Simply use your preferred cable ties or hook and loop straps.

Open Back Design - Backless design allows the rack to be installed over existing equipment such as network or electrical conduit, wall mounted equipment, and more. Perfect for upgrading a network that already is in use because you don't have to disconnect cables and spend time re-terminating. Just feed the device through the top, back, or sides and mount into place.

www.kendallhoward.com

KENDALL HOWARD



- One set of 10-32 tapped rails
- 150 lb. weight capacity
- 20" usable mounting depth
- 19" EIA-310-D compliant
- Ships knocked down

SPECIFICATIONS



Size	12U	18U
Part Number	1915-3-800-12	1915-3-800-18
Width	21.09"	21.09″
Depth	22.12"	22.12"
Height	31.24"	41.74"
Material(s)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)
Finish/Color	Black Powder Coat Finish	Black Powder Coat Finish
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground

www.kendallhoward.com