

# ECONOMICAL DEPENDABLE SAFE

With a Rebel Self Retracting Lifeline (SRL), you get an economical fall protection solution that won't compromise the safety or performance of your crew. Rebel continues to set performance standards beyond compliance, while providing a substantial value compared to competitive models.

- Improved Shock Pack Design (6' - 20' Units)
- Rugged, Lightweight Housing
- Recessed Labels To Increase Product Life
- Impact Indicator
- Swiveling Anchorage
- 3,600 Lb. Gate Capacity
- 420 Lb. Models Available (33' units and above)



**3100432**  
**REBEL 20 Ft. (6.1 m) SRL**

20 ft. (6.1 m) of 1" (2.5 cm) polyester web with steel swiveling snap hook, swiveling anchorage and carabiner.



**3590019**  
**REBEL 15 Ft. (4.5 m) SRL**

15 ft. (4.5 m) of 3/16" (5 mm) galvanized steel wire rope with steel swiveling snap hook, swiveling anchorage and carabiner.



**3100425**  
**REBEL 11 Ft. (3.3 m) SRL**

11 ft. (3.3 m) of 1" (2.5 cm) polyester web with steel snap hook, swiveling anchorage and carabiner.



# DOZENS OF WAYS TO STAY COMPLIANT WITHOUT COMPROMISE

Lifeline Material	Thermoplastic Housing	Aluminum Housing	Stackable	Impact Indicator	Swiveling Anchorage	Self Locking Snap Hook	Rebar Hook	Swiveling Hook	Leading Edge	100% Tie-Off	310 lb. (140 kg) Weight Capacity	420 lb. (190 kg) Weight Capacity	Web/Cable Length										
													6' (1.8 m)	11' (3.3 m)	15' (4.5 m)	20' (6 m)	33' (10 m)	50' (15 m)	66' (20 m)	85' (26 m)	100' (30 m)		
Galv Cable	•				•	•		•			•	•	3590015	3590016	3590019								
	•				•	•					•				3590018								
	•	•	•	•	•	•		•			•					3590517	3590500	3590550	3590590	3590630	3590670		
	•	•	•	•	•	•		•			•					3590514	3590510	3590560	3590600	3590640	3590680		
	•				•	•		•	•		•					3590540							
	•				•	•	•				•					3590020							
SS Cable	•	•	•	•	•	•		•			•					3590504	3590501	3590551	3590591	3590631	3590671		
	•	•	•	•	•	•		•			•					3590509	3590511	3590561	3590601	3590641	3590681		
Web	•				•	•					•		3100403	3100425		3100431							
	•				•	•		•			•		3100404	3100426		3100432							
	•				•	•	•				•		3100405	3100427		3100433							
	•				•	•				•	•		3100412										
	•				•	•		•			•		3100413										
	•				•	•	•				•		3100414										
													Weight	Varies	Varies	Varies	Varies	13.5 lb. (6.1 kg)	17.3 lb. (7.8 kg)	22 lb. (10 kg)	28.6 lb. (13 kg)	29.5 lb. (13.4 kg)	
													Approximate depth	2" (5 cm)	3" (8 cm)	3" (8 cm)	4.6" (12 cm)	4.6" (12 cm)	4.6" (12 cm)	5.5" (14 cm)	5.5" (14 cm)	5.5" (14 cm)	
													Approximate width	3.5" (8.9 cm)	6" (15 cm)	6" (15 cm)	9.8" (14 cm)	9.8" (24.9 cm)	11" (28 cm)	12.8" (33 cm)	12.8" (33 cm)	12.8" (33 cm)	
													Approximate height*	19" (48 cm)	19" (48 cm)	29" (74 cm)	22.5" (57.1 cm)	22.5" (57.1 cm)	23.8" (61 cm)	25.7" (65 cm)	25.7" (65 cm)	25.7" (65 cm)	

\*Anchor point to anchor point

Standards: Meets OSHA 1926.502, OSHA 1910.66, ANSI Z359.1, ANSI Z359.12, ANSI A10.32, CSA Z259.2.2 Type II



Capital Safety  
 USA: 800 328 6146  
[www.capitalsafety.com](http://www.capitalsafety.com) [info@capitalsafety.com](mailto:info@capitalsafety.com)

[@Capital\\_Safety](https://twitter.com/Capital_Safety) [Facebook.com/CapitalSafety](https://facebook.com/CapitalSafety)

**FOR MORE INFORMATION VISIT US AT CAPITALSAFETY.COM**