

SERIES 35 HAND GRINDER MODEL 8555-210

This Dumore grinder idles at 35,000 RPM. The Dumore manufactured motor provides ample power to handle grinding applications using rotary files. Three precision grease lubricated bearings give rigid spindle support for extended use and minimal run-out. The back mounted "on-off" switch prevents accidental tripping. The die-cast aluminum housing is lightweight, yet strong and durable. This unit includes a two piece collet for quick tool change.



- 1/4 HP
Universal
Motor
- 35,000 RPM
- 1/4" Chuck
- 1/8" Reducer
- 11" Overall
length
- 115V AC/DC
- Net weight
3 lbs 8 oz
- 1" mounted
wheel capacity

**Contact your local Dumore
distributor and...**

Do More with DUMORE

Don't get a cheap knockoff, get this long lasting American made product that is one of industry's most efficient die grinders for decades. Built by the hard working men and women here in Mauston, Wisconsin.



DUMORE CORPORATION

1030 Veterans Street
Mauston, WI 53948

Phone: 888-467-8288
Fax: 800-338-6673
E-mail: sales@dumorecorp.com