

Installation Kits — Solid Wall Inserts for Metal



Everything needed to repair or reinforce tapped holes in metal in a convenient, easy-to-order kit.

Featuring E-Z LOK solid wall inserts

- Strong: solid steel design with superior pull out resistance.
- Self-Locking : preapplied Loctite adhesive activates upon installation.
- Ideal for use in soft metals, like aluminum, magnesium, and cast iron.
- Easy to install: simply drill, tap and thread into place.
- Screw Locking available for high vibration applications.

Each kit includes threaded Inserts (10), drill, tap, and drive tool.

| Part Number | Int. Thread | Ext. Thread |
|-----------------------------|-------------|-------------|
| Standard Wall - Inch | | |
| EZ-329-008 | 8-32 | 5/16-18 |
| EZ-329-3 | 10-24 | 3/8-16 |
| EZ-329-332 | 10-32 | 3/8-16 |
| EZ-329-4 | 1/4-20 | 7/16-14 |
| EZ-329-428 | 1/4-28 | 7/16-14 |
| EZ-329-5 | 5/16-18 | 1/2-13 |
| EZ-329-524 | 5/16-24 | 1/2-13 |
| EZ-329-6 | 3/8-16 | 9/16-12 |
| EZ-329-624 | 3/8-24 | 9/16-12 |
| EZ-329-7 | 7/16-14 | 5/8-11 |
| EZ-329-720 | 7/16-20 | 5/8-11 |
| EZ-329-8 | 1/2-13 | 3/4-10 |
| EZ-329-820 | 1/2-20 | 3/4-10 |
| EZ-329-9 | 9/16-12 | 3/4-10 |
| EZ-329-918 | 9/16-18 | 3/4-10 |

| Part Number | Int. Thread | Ext. Thread |
|-------------------------------|-------------|-------------|
| Standard Wall - Metric | | |
| EZ-450-4 | M4-0.7 | M8-1.25 |
| EZ-450-5 | M5-0.8 | M8-1.25 |
| EZ-450-6 | M6-1.0 | M10-1.5 |
| EZ-450-8 | M8-1.25 | M12-1.75 |

| Part Number | Int. Thread | Ext. Thread |
|-------------------------|-------------|-------------|
| Thin Wall - Inch | | |
| EZ-310-3 | 10-24 | 5/16-18 |
| EZ-310-332 | 10-32 | 5/16-18 |
| EZ-310-4 | 1/4-20 | 3/8-16 |
| EZ-310-428 | 1/4-28 | 3/8-16 |

| Part Number | Int. Thread | Ext. Thread |
|-------------------------|-------------|-------------|
| Thin Wall - Inch | | |
| EZ-310-5 | 5/16-18 | 7/16-14 |
| EZ-310-524 | 5/16-24 | 7/16-14 |
| EZ-310-6 | 3/8-16 | 1/2-13 |
| EZ-310-624 | 3/8-24 | 1/2-13 |
| EZ-310-7 | 7/16-14 | 9/16-12 |
| EZ-310-720 | 7/16-20 | 9/16-12 |
| EZ-310-8 | 1/2-13 | 5/8-11 |
| EZ-310-820 | 1/2-20 | 5/8-11 |

| Part Number | Int. Thread | Ext. Thread |
|--------------------------------|-------------|-------------|
| Thin Wall - Metric/Inch | | |
| EZ-310-M4 | M4-0.7 | 5/16-18 |
| EZ-310-M5 | M5-0.8 | 5/16-18 |
| EZ-310-M6 | M6-1.0 | 3/8-16 |
| EZ-310-M8 | M8-1.25 | 7/16-14 |
| EZ-310-M10 | M10-1.5 | 1/2-13 |
| EZ-310-M12 | M12-1.75 | 5/8-11 |

| Part Number | Int. Thread | Ext. Thread |
|---------------------------------------|-------------|-------------|
| Screw Locking* - Standard Wall | | |
| EZ-329-3IC | 10-24 | 3/8-16 |
| EZ-329-332IC | 10-32 | 3/8-16 |
| EZ-329-4IC | 1/4-20 | 7/16-14 |
| EZ-329-5IC | 5/16-18 | 1/2-13 |
| EZ-329-6IC | 3/8-16 | 9/16-12 |
| EZ-329-8IC | 1/2-13 | 3/4-10 |

*Screw locking inserts include preapplied Loctite threadlocker on internal threads.

