


privacy screens

privacy screens

- ¾" anodized aluminum frames
- panels are fire-resistant
- foldable screens store away easily
- light-weight and practical
- easy-to-clean, 6-mil white vinyl curtains (default)
- yellow, 4-mil or green, 6-mil vinyl curtains available
- available with or without casters

vinyl color options



standard
3-panel
no casters

standard privacy screens

		extended size	folded size		
65-0100	W/Y/G	2-panel	35"W x 68"H	19"W x 68"H x 1½"D	122.50
65-0101	W/Y/G	3-panel	48"W x 68"H	19"W x 68"H x 2½"D	140.00
65-0102	W/Y/G	4-panel	62"W x 68"H	19"W x 68"H x 3¼"D	187.50
65-0103	W/Y/G	5-panel	84"W x 68"H	19"W x 68"H x 4"D	260.00



king size privacy screens

king size
2-panel
no casters

			extended size	folded size	
65-0120	W/Y/G	2-panel	59"W x 68"H	31"W x 68"H x 1½"D	152.50
65-0121	W/Y/G	3-panel	85"W x 68"H	31"W x 68"H x 2½"D	175.00
65-0122	W/Y/G	4-panel	113"W x 68"H	31"W x 68"H x 3½"D	230.00

standard privacy screen with casters

			extended size	
65-0110	W/Y/G	3-panel	48"W x 68"H	142.50
65-0111	W/Y/G	4-panel	62"W x 68"H	212.20



standard
4-panel
with
casters



king size privacy screen with casters

			extended size	
65-0131	W/Y/G	3-panel	85"W x 68"H	195.00



king size
3-panel
with
casters

