

PRODUCT SPECIFICATIONS

FlowTech 1-D Full Body Harness

#7087L

Features

- One d-ring for fall arrest and positioning.
- 5-point adjustability.
- Quick-connect leg straps.
- Padded shoulder yoke.
- 2 lanyard keepers.
- Aluminum hardware for lighter weight.
- Extreme duty, removable workbelt.
- Size: Large

Material Specifications

Webbing: *Polyester; Min. 5,000 lbs. tensile strength*

D-Rings: *Alloy Steel; Min. 5,000 lbs. tensile strength*

Buckles/Adjusters: *Aluminum; Min. 3,375 lbs. tensile strength*

Performance Specifications

Tensile Strength: *Min. 5,000 lbs.*

Max. Capacity: *425 lbs.*

Relevant Standards

OSHA: *CFR1926.502, CFR1910.66*

ANSI: *A10.32-2004, Z359.1-2007, Z359.12-2009*

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.
- Never attach a Shock Absorbing Lanyard to the front or side D-Rings.



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com

WARNING: THIS SPECIFICATION SHEET PROVIDES AN OVERVIEW OF PRODUCTS AVAILABLE FROM FALLTECH. CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE INFORMATION. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. FALLTECH RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THESE PRODUCTS BE THOROUGHLY READ UNDERSTOOD PRIOR TO USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.