

PRODUCT SPECIFICATIONS

Contractor 50' SRL

#727650

Features

- Rugged, lightweight design. Full inertial brake mechanism.
- Load-indicating swivel carabiner with 3,600 lb. gate.
- Rated for one worker up to 310 lbs.
- Meets ANSI Z359.1-2007, ANSI A10.32 and applicable OSHA requirements.

Material Specifications

Cable:	<i>3/16", 7X19 galvanized steel</i>
Connector:	<i>Alloy Steel; Min. 5,000 lbs. tensile strength</i>
Connector Gates:	<i>Alloy Steel; Min. 3,600 lbs. front load and side load</i>

Performance Specifications

Tensile Strength:	<i>Min. 5,000 lbs.</i>
Max. Capacity:	<i>310 lbs.</i>

Relevant Standards

OSHA:	<i>CFR1926.502, CFR1910.66</i>
ANSI:	<i>A10.32-2004</i>

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.
- Never attach a Restraint Lanyard to the front or side D-Rings.



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com

WARNING: THIS SPECIFICATION SHEET PROVIDES AN OVERVIEW OF PRODUCTS AVAILABLE FROM FALLTECH. CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE INFORMATION. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. FALLTECH RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THESE PRODUCTS BE THOROUGHLY READ UNDERSTOOD PRIOR TO USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.