

Homak

SINCE 1947.

3.5 GALLON PARTS WASHER

Product Features:



Electronic ON/OFF Switch
Controls Pump Operation



Flexible Spray Nozzle



Fusible Linked Lid Arm
Prevents Accidental Injuries
In Case Of Fire



Removable Work Surface
Tray With Drain Holes



Replaceable Electric Pump
With 0.6 GPM Flow Rate



Full-Length, Welded
Piano Hinge

**1 YEAR**
LIMITED WARRANTY

3.5 GALLON PARTS WASHER

- Fusible Linked Lid Arm To Prevent Accidental Injury In Case Of Fire
- 3.2 mil Epoxy-Polyester Powder Coat Paint Finish
- Single-Piece Tank For Cleaning Small Parts
- Solid Steel Design That Won't Leak
- Removable Work Surface Tray
- 0.6 GPM Max Flow Rate
- Electric Pump Included
- Pump ON/OFF Switch
- Flexible Nozzle

Product Specifications:

PARTS WASHER	WIDTH	DEPTH	HEIGHT	CAPACITY
Solvent Tank	15 1/4"	11 5/8"	5 1/2"	0.56 cu ft

METAL THICKNESS

Frame	1.0 mm
Legs	1.5 mm

MAXIMUM CAPACITIES

Tank	110 lbs
------	---------



MODEL No.	PRODUCT DESCRIPTION	WIDTH	DEPTH	HEIGHT	PC WT	SHIPWT	UPC CODE
RD00803180	3.5 Gallon Parts Washer	17"	13 1/2"	9"	15 lbs.	17 lbs.	034518 01009 1

1.800.874.6625**www.Homak.com**