



40 GALLON PARTS WASHER

Product Features:



Washing Basket For Cleaning of Smaller Parts



Fusible Linked Lid Arm Prevents Accidental Injuries In Case Of Fire



Electronic ON/OFF Switch Controls Pump Operation



Flexible Spray Nozzle



Bottom Storage Shelf for Extra Space



40 GALLON PARTS WASHER

- Fusible Linked Lid Arm To Prevent Accidental Injury In Case Of Fire
- Includes Washing Basket for Cleaning Smaller Parts
- 3.2 mil Epoxy-Polyester Powder Coat Paint Finish
- Large One Piece Tank For Cleaning Big Parts
- Solid Steel Design That Won't Leak
- Removable Work Surface Tray
- 5.6 GPM Max Flow Rate
- Electric Pump Included
- Pump ON/OFF Switch
- Flexible Nozzle

Product Specifications:

PARTS WASHER	WIDTH	DEPTH	HEIGHT	CAPACITY
Solvent Tank	41 7/8"	20 1/2"	10 1/4"	5.1 cu ft
Parts Basket	9 1/2"	6"	3 1/2"	0.12 cu ft
Storage Shelf	38"	16 3/4"	13"	4.79 cu ft

METAL THICKNESS	
Frame	1.0 mm
Legs	1.5 mm

MAXIMUM CAPACITIES	
Tank	110 lbs
Drying Shelf	110 lbs
Recovery Bin	110 lbs
Storage Shelf	110 lbs



MODEL No.	PRODUCT DESCRIPTION	WIDTH	DEPTH	HEIGHT	PC WT	SHIPWT	UPC CODE
RD00840450	40 Gallon Parts Washer	46 7/8"	22 7/8"	36 3/4"	93 lbs.	99 lbs.	034518 01007 7

1.800.874.6625

www.Homak.com