


FirmFit™



**Simple Formula.
More Comfort.**



The more comfortable the earplug,
the longer they'll wear it.

FirmFit™

Some workers prefer firm foam earplugs.
They deserve the best in firm foam.

We've Listened to Workers.

Extensive research into earplug preferences revealed that some workers prefer a firm foam earplug. They gain a sense of security from feeling the earplug in their ear. And while they like knowing the earplug is there, workers want greater comfort. FirmFit outperforms leading classic-style earplugs, providing workers with a more comfortable option.

Softness you can feel

You can feel that FirmFit is soft when you hold it.

Less Pressure

FirmFit exerts low expansion pressure on the ear canal.

Greater Protection

NRR 30dB provides excellent protection in most medium-to-high noise environments.

Easy to insert

Requires less pressure to roll down. Slow recovery rate gives you plenty of time to correctly insert in ear canal.

Easy to see

Distinct warning orange color makes compliance checks easy.

**Longer wear time comfort:
More protection. Greater compliance.**



FirmFit™ Ordering Information

| Part # | Description | Packaging | Unit of Measure |
|----------|------------------------------------|----------------------------|-----------------|
| FF-1 | FirmFit uncorded | polybag, 200 pair per box | Box of 200 |
| FF-30 | FirmFit corded | polybag, 100 pair per box | Box of 100 |
| FF-1-PB | FirmFit uncorded, paperbag | paperbag, 100 pair per box | Box of 100 |
| FF-30-PB | FirmFit corded, paperbag | paperbag, 100 pair per box | Box of 100 |
| FF-1-D | FirmFit uncorded, dispenser refill | 500 pair per box | Box of 500 |
| FF-LS4 | FirmFit uncorded, dispenser refill | 200 pair per box | Box of 200 |

FirmFit™ Attenuation Data

Howard Leight® (FirmFit™) is tested according to ANSI S3.19-1974 at Michael & Associates, Inc.

Region – USA

| | | | | | | | | | | |
|------------------------|------|------|------|------|------|------|------|------|------|-----------|
| Frequency Hz | 125 | 250 | 500 | 1000 | 2000 | 3150 | 4000 | 6300 | 8000 | NRR Value |
| Mean Value, dB | 33.9 | 33.1 | 38.1 | 37.0 | 39.7 | 46.1 | 45.5 | 47.7 | 47.0 | 30 dB |
| Standard Deviation, dB | 5.5 | 4.0 | 3.8 | 3.4 | 3.7 | 2.5 | 4.6 | 3.9 | 3.9 | |

The global leader in hearing conservation.

For more than 30 years, we have pursued the prevention of occupational hearing loss through innovations in hearing protection design, technology, performance, comfort, and the promotion of progressive Hearing Conservation programs. Because your workers deserve the best in hearing protection.



Find out more and request free samples. HowardLeight.com/FirmFit

Honeywell Safety Products
900 Douglas Pike
Smithfield, RI 02917

Phone 800.430.5490
Fax 401.232.3112
www.howardleight.com



by Honeywell

Lead them to safety. Honeywell can help.

HLLI.108 06/15

Honeywell