

RACK SCREWS (10-32, 12-24, M5, M6)

AMERICAN
MADE 



The Kendall Howard Rack Screws are not your everyday hardware store item. The superior American-made quality should be your only choice for installing rack mount devices such as shelves, cable managers, servers, and other network, A/V and electronic equipment.

- 0.75" in length
- Phillips truss head
- Packaged in an aluminum tin
- RoHS Compliant
- Made in the USA



FEATURES

Dog/Pilot Point - The straight pointed section below the thread helps to self-guide the screw to prevent accidental stripping while also improving the ease of installation.

Phillips Truss Head - Truss head screws can be installed with one of the most universal tools on the market. Requires only a Phillips head screwdriver or bit.

Compatible Rail Systems - Kendall Howard rack screws can be utilized in any tapped rail system. They can also be installed in universal cage nut style rails when used in conjunction with cage nuts.

Superior Manufacturing - The cold hardened steel construction produces a high-quality finish with excellent dimensional stability. We then take it one step further and finish them with a black oxide coating so the screw blends with most standard black network racks, cabinets, and accessories.

10-32 Rack Screw Specifications

Thread Size	10-32	10-32	10-32	10-32
Quantity	50	100	2500	5000
Part Number	0100-1-001-01	0100-1-002-01	0100-3-200-01	0100-3-100-01
Width	0.44"	0.44"	0.44"	0.44"
Depth	0.87"	0.87"	0.87"	0.87"
Height	0.44"	0.44"	0.44"	0.44"
Material(s)	Hardened Steel	Hardened Steel	Hardened Steel	Hardened Steel
Finish/Color	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish
UPC	879447000030	879447000047	879447000092	879447000078
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground	FedEx Ground	FedEx Ground

12-24 Rack Screw Specifications

Thread Size	12-24	12-24	12-24	12-24
Quantity	50	100	2500	5000
Part Number	0100-1-001-03	0100-1-002-03	0100-3-200-03	0100-3-100-03
Width	0.51"	0.51"	0.51"	0.51"
Depth	0.88"	0.88"	0.88"	0.88"
Height	0.51"	0.51"	0.51"	0.51"
Material(s)	Hardened Steel	Hardened Steel	Hardened Steel	Hardened Steel
Finish/Color	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish
UPC	879447002881	879447002911	879447003031	879447003000
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground	FedEx Ground	FedEx Ground

M5 Rack Screw Specifications

Thread Size	M5	M5	M5	M5
Quantity	50	100	2500	5000
Part Number	0100-1-001-02	0100-1-002-02	0100-3-200-02	0100-3-100-02
Width	0.43"	0.43"	0.43"	0.43"
Depth	0.87"	0.87"	0.87"	0.87"
Height	0.43"	0.43"	0.43"	0.43"
Material(s)	Hardened Steel	Hardened Steel	Hardened Steel	Hardened Steel
Finish/Color	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish
UPC	879447002874	879447002904	879447003024	879447002997
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	Ships Fedex Ground	Ships Fedex Ground	Ships Fedex Ground	Ships Fedex Ground

M6 Rack Screw Specifications

Thread Size	M6	M6	M6	M6
Quantity	50	100	2500	5000
Part Number	0100-1-001-04	0100-1-002-04	0100-3-200-04	0100-3-100-04
Width	0.55"	0.55"	0.55"	0.55"
Depth	0.94"	0.94"	0.94"	0.94"
Height	0.55"	0.55"	0.55"	0.55"
Material(s)	Hardened Steel	Hardened Steel	Hardened Steel	Hardened Steel
Finish/Color	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish	Black Oxide with Wax Finish
UPC	879447002898	879447002928	879447003048	879447003017
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	Ships Fedex Ground	Ships Fedex Ground	Ships Fedex Ground	Ships Fedex Ground