
FLANGED LACING BARS





Properly manage and protect your cables with the Kendall Howard Flanged Lacing Bar. Its size and versatility make it a true space saving cable manager. Designed to mount above, below, behind, or in front of your network devices, the Flanged Lacing Bar allows you to do more by using less space. And that's not all. It provides a much needed stress relief for cable connections, and works well when routing cables between switches and patch panels. Crowded spaces, unorganized cables, and strained connections are no longer an issue with the Kendall Howard Flanged Lacing Bar.

When extra depth is needed, the 3" D and 5" D Flanged Lacing Bars are the perfect solution. These bars promote a good bend radius for network cables, and limit the risk of slower data speeds and broken cables.

FEATURES


Space Saver - Mount the bar above, below, behind, or in front of your network device, vacating valuable U space for other network installation needs. The bar itself uses less than one U space, or none at all if mounted in front of or behind equipment.

Numerous Cable Lacing Points - Lacing slots are included on both flanges allowing you to route cables top to bottom or left to right. These lacing slots also nearly cover the entire length of the panel allowing convenient routing to both ends.

Strain Reliever - Designed to relieve cable stress and avoid pulling cables when routing them from one side of a rack to the other.

Promotes Good Bend Radius - The 3" D and 5" D Flanged Lacing Bars promote a good bend radius for cables, therefore limiting the risk of slower data speeds and broken cables.

KENDALL HOWARD



- Features $\frac{1}{2}$ " slots to use with any $\frac{1}{2}$ " cable ties
- Uses less than one U space, or none at all if mounted in front of or behind equipment
- Versatile, horizontal mounting
- 19" EIA 310-D compliant
- Made in the USA
- Limited Lifetime Warranty

SPECIFICATIONS

Size	Standard	3" Depth	5" Depth
Part Number	1903-1-100-00	1903-1-101-00	1903-1-102-00
10 Pack Part Number	1903-1-110-00	1903-1-111-00	1903-1-112-00
Width	19"	19"	19"
Depth	1"	3"	5"
Height	0.583"	0.563"	0.563"
Material(s)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)
Finish/Color	Black Powder Coat Finish	Black Powder Coat Finish	Black Powder Coat Finish
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground	FedEx Ground