

LINIER[®] SERVER CABINETS - 36" DEPTH



The Kendall Howard LINIER[®] Server Cabinets are packed with some of the most popular rack features at a price virtually anyone can afford. The cabinets feature laser knockouts allowing you to install fans, while removable slots provide numerous cable routing options. Built with a 36" depth, these LINIER[®] cabinets are suitable for network servers, battery backups, switching banks, and other larger network equipment. To suit your particular network install, numerous door configurations are available (including glass, solid, vented, and convex doors), and we even offer cabinets without doors and/or without side panels. When you need a low cost solution packed with features, the LINIER[®] Server Cabinets deliver!

- 1300 lb. weight capacity (800 lbs. on casters)
- Preinstalled casters and levelers
- Includes two sets of adjustable cage nut style mounting rails
- Removable locking side panels
(Feature not applicable to 3170 series)
- Top includes removable laser knockouts
- 19" EIA 310-D compliant
- Made in the USA
- 5-Year Limited Warranty

FEATURES

Easy Installation - Casters and levelers are preinstalled to allow you to easily move and load your system into the desired location. (Rack hardware not included.)

Removable Cable Access Panels - The top of the server cabinet includes removable laser knockouts for cable access and added versatility.

Locking, Removable Side Panels - For a completely different look, the side panels are both removable and lockable giving you the option to create the cabinet that best suits your needs. (Feature not applicable to 3170 series)

Adjustable Rails - Includes two sets of adjustable, vertical rails which extend to a maximum depth of 36" for versatile mounting options.

Secured System - Both doors are equipped with locks to help protect and secure your valuable equipment.
(Feature not applicable to 3170 and 3180 series)

GLASS DOOR



SOLID DOOR



VENTED DOOR



CONVEX DOOR



NO DOORS/NO SIDE PANELS



NO DOORS



22U SPECIFICATIONS

| Door 1 | Door 2 | Part Number | Dimensions |
|-------------------------|--------|---------------|-----------------------------|
| Glass | Vented | 3100-3-001-22 | 24" W x 37.72" D x 45.50" H |
| Glass | Solid | 3101-3-001-22 | 24" W x 37.72" D x 45.50" H |
| Convex | Glass | 3102-3-001-22 | 24" W x 38.22" D x 45.50" H |
| Glass | Glass | 3103-3-001-22 | 24" W x 37.72" D x 45.50" H |
| Solid | Convex | 3104-3-001-22 | 24" W x 38.22" D x 45.50" H |
| Convex | Convex | 3105-3-001-22 | 24" W x 38.72" D x 45.50" H |
| Solid | Vented | 3106-3-001-22 | 24" W x 37.72" D x 45.50" H |
| Vented | Vented | 3107-3-001-22 | 24" W x 37.72" D x 45.50" H |
| Solid | Solid | 3108-3-001-22 | 24" W x 37.72" D x 45.50" H |
| Convex | Vented | 3110-3-001-22 | 24" W x 38.22" D x 45.50" H |
| No Doors/No Side Panels | | 3170-3-001-22 | 24" W x 37.72" D x 45.50" H |
| No Doors | | 3180-3-001-22 | 24" W x 37.72" D x 45.50" H |

27U SPECIFICATIONS

| Door 1 | Door 2 | Part Number | Dimensions |
|-------------------------|--------|---------------|-----------------------------|
| Glass | Vented | 3100-3-001-27 | 24" W x 37.72" D x 54.25" H |
| Glass | Solid | 3101-3-001-27 | 24" W x 37.72" D x 54.25" H |
| Convex | Glass | 3102-3-001-27 | 24" W x 38.22" D x 54.25" H |
| Glass | Glass | 3103-3-001-27 | 24" W x 37.72" D x 54.25" H |
| Solid | Convex | 3104-3-001-27 | 24" W x 38.22" D x 54.25" H |
| Convex | Convex | 3105-3-001-27 | 24" W x 38.72" D x 54.25" H |
| Solid | Vented | 3106-3-001-27 | 24" W x 37.72" D x 54.25" H |
| Vented | Vented | 3107-3-001-27 | 24" W x 37.72" D x 54.25" H |
| Solid | Solid | 3108-3-001-27 | 24" W x 37.72" D x 54.25" H |
| Convex | Vented | 3110-3-001-27 | 24" W x 38.22" D x 54.25" H |
| No Doors/No Side Panels | | 3170-3-001-27 | 24" W x 37.72" D x 54.25" H |
| No Doors | | 3180-3-001-27 | 24" W x 37.72" D x 54.25" H |

37U SPECIFICATIONS

| Door 1 | Door 2 | Part Number | Dimensions |
|-------------------------|--------|---------------|-----------------------------|
| Glass | Vented | 3100-3-001-37 | 24" W x 37.72" D x 71.75" H |
| Glass | Solid | 3101-3-001-37 | 24" W x 37.72" D x 71.75" H |
| Convex | Glass | 3102-3-001-37 | 24" W x 38.22" D x 71.75" H |
| Glass | Glass | 3103-3-001-37 | 24" W x 37.72" D x 71.75" H |
| Solid | Convex | 3104-3-001-37 | 24" W x 38.22" D x 71.75" H |
| Convex | Convex | 3105-3-001-37 | 24" W x 38.72" D x 71.75" H |
| Solid | Vented | 3106-3-001-37 | 24" W x 37.72" D x 71.75" H |
| Vented | Vented | 3107-3-001-37 | 24" W x 37.72" D x 71.75" H |
| Solid | Solid | 3108-3-001-37 | 24" W x 37.72" D x 71.75" H |
| Convex | Vented | 3110-3-001-37 | 24" W x 38.22" D x 71.75" H |
| No Doors/No Side Panels | | 3170-3-001-37 | 24" W x 37.72" D x 71.75" H |
| No Doors | | 3180-3-001-37 | 24" W x 37.72" D x 71.75" H |

42U SPECIFICATIONS

| Door 1 | Door 2 | Part Number | Dimensions |
|-------------------------|--------|---------------|-----------------------------|
| Glass | Vented | 3100-3-001-42 | 24" W x 37.72" D x 80.50" H |
| Glass | Solid | 3101-3-001-42 | 24" W x 37.72" D x 80.50" H |
| Convex | Glass | 3102-3-001-42 | 24" W x 38.22" D x 80.50" H |
| Glass | Glass | 3103-3-001-42 | 24" W x 37.72" D x 80.50" H |
| Solid | Convex | 3104-3-001-42 | 24" W x 38.22" D x 80.50" H |
| Convex | Convex | 3105-3-001-42 | 24" W x 38.72" D x 80.50" H |
| Solid | Vented | 3106-3-001-42 | 24" W x 37.72" D x 80.50" H |
| Vented | Vented | 3107-3-001-42 | 24" W x 37.72" D x 80.50" H |
| Solid | Solid | 3108-3-001-42 | 24" W x 37.72" D x 80.50" H |
| Convex | Vented | 3110-3-001-42 | 24" W x 38.22" D x 80.50" H |
| No Doors/No Side Panels | | 3170-3-001-42 | 24" W x 37.72" D x 80.50" H |
| No Doors | | 3180-3-001-42 | 24" W x 37.72" D x 80.50" H |