

FS30LVAC



24.63" x 18.5" x 17.75" (H x W x D)

Countertop vaccine storage all-freezer with digital thermostat, temperature alarm, hospital grade cord, self-closing door, and front lock

Highlights:

Medical grade design conforms with CDC guidelines for vaccine storage

Compact size is ideal for countertop use

Digital thermostat ensures more precision in temperature control

Product Features:

| | |
|---|--|
| Compact dimensions | Sized for easy use on top of counters |
| Digital thermostat | Electronic controls ensure easy and intuitive temperature management, with a readout in Celsius or Fahrenheit |
| High/low temperature alarm | Audible alarm sounds if the interior temperature rises or falls out of set range |
| NIST calibrated temperature display | Alarm includes NIST calibrated display of the current interior and high/low temperature to the nearest tenth of a degree |
| Self-closing door | Door closes automatically when opened at angles less than 90° |
| Access port with contact | Pre-installed probe with contact allows users to install their own monitoring equipment; customers can specify placement of the access port upon order |
| Hospital grade cord with 'green dot' plug | Secure three-pronged cord for added unit safety |
| Manual defrost | Static cooling system for improved temperature stability |
| Factory installed lock | Keyed lock for a secure interior |

FS30LVAC Specifications:

| Overview | |
|----------------------------|--------------------|
| Height of Cabinet | 26.25" (67 cm) |
| Height to Hinge Cap | 24.63" (63 cm) |
| Width | 18.5" (47 cm) |
| Depth | 17.75" (45 cm) |
| Depth with door at 90° | 34.5" (88 cm) |
| Capacity | 1.8 cu.ft. (51 L) |
| Defrost Type | Manual |
| Door | White |
| Cabinet | White |
| US Electrical Safety | ETL |
| Canadian Electrical Safety | ETL-C |
| Amps | 0.8 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Weight | 50.0 lbs. (23 kg) |
| Shipping Weight | 60.0 lbs. (27 kg) |
| Parts & Labor Warranty | 2 Years |
| Compressor Warranty | 5 Years |
| Freezer | |
| Door Swing | RHD |
| Reversible | Factory Reversible |
| Interior Height | 18.63" (47 cm) |
| Interior Width | 13.38" (34 cm) |
| Interior Depth | 13.0" (33 cm) |
| Shelf Type | Wire |
| Shelf Qty | 2 |
| Thermostat Type | Digital |
| Refrigerant Type | R600a |
| Refrigerant Amount | 0.8 oz. |
| Level Legs | 2 |
| Compressor Step Height | 8.0" (20 cm) |
| Compressor Step Width | 13.38" (34 cm) |
| Compressor Step Depth | 5.75" (15 cm) |

