

ACF48WADA



32" x 23.63" x 23.5" (H x W x D)

Built-in ADA compliant undercounter frost-free all-freezer for general purpose use, with white exterior, digital thermostat, and lock

Highlights:

32 inch height fits under lower ADA compliant counters

Digital thermostat offers more precision in temperature management

Frost-free operation ensures low maintenance use

Flexible design allows built-in or freestanding use in 24" spaces

Product Features:

| | |
|------------------------------|--|
| ADA Compliant | 32 inch height is designed to fit under ADA compliant counters |
| Built-in capable | Make the best use of space by installing your appliance under the counter and flush with other cabinetry |
| Slim undercounter dimensions | Sized at less than 24" wide and deep for an easy fit in space-challenged institutions |
| Frost-free operation | Low maintenance design ensures no frost buildup inside the unit |
| Digital temperature control | Electronic controls located in the exterior kickplate for precise temperature management |
| Factory installed lock | Keyed lock for added security, located towards the top of the door to ensure convenient access |
| Internal fan | Fan-forced cooling ensures the unit is evenly cooled from top to bottom |
| Removable shelves | Includes two slide-out shelves made from durable steel |
| Hospital grade cord | Secure three-pronged cord for added unit safety |

ACF48WADA Specifications:

| Overview | |
|----------------------------|-------------------------|
| Height | 32.0" |
| Height to Hinge Cap | 32.25" |
| Width | 23.63" |
| Depth | 23.5" |
| Depth with Handle | 24.25" |
| Depth with door at 90° | 45.13" |
| Capacity | 3.1 cu.ft. |
| Defrost Type | Frost-Free |
| Door | White |
| Cabinet | White |
| US Electrical Safety | ETL |
| Canadian Electrical Safety | ETL-C |
| Amps | 1.5 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Weight | 100.0 lbs. |
| Shipping Weight | 110.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Freezer | |
| Door Swing | RHD |
| Reversible | Yes |
| Shelf Type | Steel |
| Shelf Qty | 2 |
| Thermostat Type | Digital |
| Fan Type | Interior and Exterior |
| Refrigerant Type | R134a |
| Refrigerant Amount | 4.2 oz. |
| High Side PSI | 285.0 |
| Low Side PSI | 70.0 |
| Level Legs | 4 |
| Temperature Range | -5 to 10°F/-20 to -12°C |

