

# ACF48WCSSADA



32" x 23.63" x 23.5" (H x W x D)

Built-in ADA compliant undercounter frost-free all-freezer for general purpose use, with stainless steel exterior, digital thermostat, and lock

## Highlights:

32" high for use under ADA compliant counters

Frost-free operation ensures low maintenance use

Digital thermostat offers more precision in temperature management

Flexible design allows built-in or freestanding use in 24" spaces

## Product Features:

Slim undercounter dimensions	Sized at less than 24" wide and deep for an easy fit in space-challenged institutions
Built-in capable	Front-breathing system allows the unit to be used built-in
Frost-free operation	Low maintenance design ensures no frost buildup inside the unit
Digital temperature control	Electronic controls located in the exterior kickplate for precise temperature management
Stainless steel wrapped exterior	Cabinet and door are wrapped in quality stainless steel to ensure lasting durability and easy cleaning
Professional towel bar handle	Curved towel bar style handle offers a solid grip in attractive brushed stainless steel
Factory installed lock	Keyed lock for added security, located towards the top of the door to ensure convenient access
Removable shelves	Includes two slide-out shelves made from durable steel
Internal fan	Fan-forced cooling ensures the unit is evenly cooled from top to bottom

**ACF48WCSSADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	23.63"
Depth	23.5"
Capacity	3.1 cu.ft.
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.5
Voltage/Frequency	115 V AC/60 Hz
Weight	120.0 lbs.
Shipping Weight	130.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Steel
Shelf Qty	2
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R134a
Refrigerant Amount	4.2 oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Temperature Range	-5 to 10°F/-20 to -12°C

