

DYMO

LabelManager[®] 420P

High-Performance Portable Label Maker with PC and Mac[®] Connection



Your team is working harder,
faster, smarter.
Choose the label maker
that's built to keep up.

LabelManager[®] 420P Features

- 1 Use standalone – or connect via USB to your PC or Mac[®] and use DYMO Label[™] Software to print barcodes, logos, batch labels from data files, and much more
- 2 Large 4-line backlit display – shows text effects on screen before you print
- 3 8 fonts, 7 font sizes, 10 text styles, 8 boxes plus underline
- 4 Quick access keys for currency and symbols
- 5 Powered by a rechargeable lithium-ion battery – no more disposable AA battery expense and inconvenience
- 6 Ideal for sharing – connect to any PC just plug, type and print – no software required
- 7 Uses DYMO D1 label cassettes in 1/4", 3/8", 1/2", and 3/4" widths



Powered by a rechargeable lithium-ion battery



DYMO[®] Label[™] Software

DYMO Label[™] v.8 Works with any fonts or graphics on your computer – customize with your company logo and much more!

Multi-application Print labels from within Microsoft[®] Word, Excel[®] or Outlook[®], Mac[®] Address Book, QuickBooks[®] and other programs

PC or Mac[®] Works with Windows[®] XP, Windows Vista[®], Windows[®] 7 or Mac OS[®] X 10.4 or later – Intel[®] only



Item # 1768815

List Price: \$149.99



D1 Labels

Standard, Permanent or Flexible...
no labels are more durable.



Standard labels* for hundreds of tasks around the office or home office, such as filing, storage, asset management, and reminders. Available in continuous label cassettes, you can create sharp, easy-to-read labels of just about any length.



Permanent labels look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely.



Flexible labels are for curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put.



Easy Peel



UV Resistant



Water Resistant



*Temperature: -40° F to 194° F

LabelManager® 420P Specifications

Item #1768815 List Price: \$149.99

LabelManager® 420P Pack Content

- Electronic label maker
- D1 starter label cassette, black on white, 3/4" x 11.5'
- Lithium-ion rechargeable battery
- Charging adapter
- USB cable
- Quick Start Guide
- 1-Year Limited Warranty Card

LM420P Pack Unit

Length	7.4"
Width	3.9"
Height	9.8"
Weight (lbs)	2.3

Shipper

Length	15.7"
Width	11.3"
Height	13.2"
Weight (lbs)	15.45

D1 labels for the LabelManager® 420P

Standard (available in 1/4", 3/8", 1/2" and 3/4" x 23') List Price: \$19.67 (1/4", 3/8", and 1/2") \$27.43 (3/4")

	BLACK•WHITE	RED•WHITE	BLACK•YELLOW	BLACK•RED	BLACK•CLEAR	RED•CLEAR
1/4"	43613	-	-	-	43610	-
3/8"	41913	40915	-	-	40910	-
1/2"	45013	45015	45018	45017	45010	45012
3/4"	45803	45805	45808	45807	45800	45802

	BLUE•WHITE	WHITE•BLACK	BLACK•BLUE	BLACK•GREEN	WHITE•CLEAR	BLUE•CLEAR
1/4"	-	-	-	-	-	-
3/8"	40914	-	-	-	-	-
1/2"	45014	45021	45016	45019	45020	45011
3/4"	45804	45811	-	45809	45810	45801

Flexible (available in 1/2" x 11.5')
List Price: \$18.80 (1/2")

	BLACK•WHITE
1/2"	16953

Permanent (available in 1/2" x 18')
List Price: \$18.80 (1/2")

	BLACK•WHITE
1/2"	16955

