## Martin Yale<sup>®</sup> 1611 & 1711 Paper Folder

## 1611

Folds 3.5" x 5" to 8.5" x 14" Fold Weights 16# Bond to 90# Text 60 gsm to 131 gsm

> 1711 Folds

3.5" x 5" to 8.5" x 14"

Fold Weights 16# Bond to 90# Text

60 gsm to 131 gsm

Fold Types:

## 1611 & 1711

• Operates at a speed of up to 9,000 sheets per hour

123457

- Easy to use, high speed folding machines for large mail rooms, associations and offices
- Feed table has a capacity of 150 sheets of 20lb bond paper
- Automatic feeding, folding and stacking documents
- Enhanced precision paper skew adjustment to keep folds crisp and accurate

martin yale\*

• Will fold stapled sets up to 5 sheets using manual bypass

Letter	Half	Z-Fold	Double Parallel	Gate	Engineering	Church
Fold	Fold		Fold	Fold	Fold	Fold
1 🔁 2	3	R	4 5		6 7	$\sum$

Martin Y	′ale® Model #	1611	1711	
Benchmark Speed	sheets/hr	9,000	9,000	
Standard paper size	inch cm	3.5 x 5 to 8.5 x 14 A4, A5	3.5 x 5 to 8.5 x 14 A4, A5, Custom	
Paper Weight		60 gsm to 131 gsm 16# Bond to 90# Text	60 gsm to 131 gsm 16# Bond to 90# Text	
Manual Paper Feed	up to sheets	5	5	
Feed Tray Capacity	up to sheets	150	150	
Power	volts	115/230	115/230	
Dimensions	<i>W</i> x D x H approx. inch cm	21 x 15.5 x 13.2 53 x 39 x 34	21 x 15.5 x 13.2 53 x 39 x 34	
Weight	approx. ounces/lbs	40 lbs.	41lbs.	

Martin Yale Industries, LLC 251 Wedcor Avenue Wabash, IN 46992 Phone: 800.225.5644 Fax: 260.563.4575 www.martinyale.com