


# WORLDWIDE FRACTIONAL HP MOTORS

## Jet Pump Motors


TEFC Enclosure ▪ C-Face ▪ Removable Base  
Single-Phase ▪ 115-208-230 Volt



### Keyed Shaft

ALL DIMENSIONS IN INCHES

Model	E	2F1	2F2	H	BA	A	B	C	D	G	J	P	L	AB
TJ13-36-56CB-NOL	2.44	3	5	0.34	2.75	6.5	6.5	12.2	3.5	0.12	1.73	6.9	8.07	5.35
TJ12-36-56CB-NOL	2.44	3	5	0.34	2.75	6.5	6.5	12.2	3.5	0.12	1.73	6.9	8.07	5.35
TJ34-36-56CB-NOL	2.44	3	5	0.34	2.75	6.5	6.5	12.2	3.5	0.12	1.73	6.9	8.07	5.35
TJ1-36-56CB-NOL	2.44	3	5	0.34	2.75	6.5	6.5	12.2	3.5	0.12	1.73	6.9	8.07	5.35
TJ1.5-36-56CB-NOL	2.44	3	5	0.34	2.75	6.5	6.5	13	3.5	0.12	1.73	6.9	8.5	5.35
TJ2-36-56CB-NOL	2.44	3	5	0.34	2.75	6.5	6.5	13	3.5	0.12	1.73	6.9	8.5	5.35



### Threaded Shaft

ALL DIMENSIONS IN INCHES

Model	E	2F1	2F2	H	BA	A	B	C	D	G	J	P	L	AB
TJ13-36-56JB	2.44	3	5	0.34	2.75	6.5	6.5	12.6	3.5	0.12	1.73	6.9	8.07	5.35
TJ12-36-56JB	2.44	3	5	0.34	2.75	6.5	6.5	12.6	3.5	0.12	1.73	6.9	8.07	5.35
TJ34-36-56JB	2.44	3	5	0.34	2.75	6.5	6.5	12.6	3.5	0.12	1.73	6.9	8.07	5.35
TJ1-36-56JB	2.44	3	5	0.34	2.75	6.5	6.5	12.6	3.5	0.12	1.73	6.9	8.07	5.35
TJ1.5-36-56JB	2.44	3	5	0.34	2.75	6.5	6.5	13.5	3.5	0.12	1.73	6.9	8.5	5.35
TJ2-36-56JB	2.44	3	5	0.34	2.75	6.5	6.5	13.5	3.5	0.12	1.73	6.9	8.5	5.35

Dimensions shown in this catalog are for general use only.  
For an exact drawing on a specific rating, please contact our sales office.

Continued On Next Page

