

HTB1040 SPEC SHEET



MODEL
HTB1040
3.5" SEAT

With
Permanent
Ganging

UPHOLSTERY OPTIONS:

1 - KFI House Upholsteries and Vinyl's

2 - Grade-In Options from:

**Mayer
Momentum
Spradling
Guilford of Maine**

3 - COM (Customer's Own Material)

A. SEAT: 3.5" Upholstered Waterfall
B. BACK: 1.5" Upholstered

C. FRAME FINISH:
1 - Sandtex Black (SB) or Silver (SL)
2 - Additional Frame Colors - 50 minimum, Call for details

D. OPTIONS:
1 - Underseat Book Rack
2 - Elastic Book Pocket
3 - Card Pocket



Chair is 95% recyclable after its useful life.*



Small Business
HUBZone

Made in USA

Specifications	Description
A - Type Frame	1" Square Tubing - 18 Gauge
B - Number of Welds	Twelve Point Welds
C - Stretcher	5/8" Round Tubing Front Stretcher
	5/8" Round Tubing Back Stretcher
D - Foam	100% Virgin Polyurethane Hi-Density California TB-117 - Standard Boston Fire Code - Optional
E - Glides Black Polyethylene	
F - Upholstery	See KFI Swatch Cards
G - Dimensions, Overall	
1 - Height	35.5"
2 - Depth	25"
3 - Width	21"
4 - Seat Size	21"W x 15.5"D
5 - Seat Height from floor	17.5"
6 - Back Dimensions	20.5" X 19.5"
H - Features	Front and back stretcher bars. 1" square tubing for added strength. Lumbar Support WEIGHT TESTED TO HOLD 500 LBS LIFE-TIME FRAME WARRANTY
I - Chair Weight	23 lbs

