



VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



VOLTAGE	L1	L2	L3	JOIN & INSULATE
HIGH	T1	T2	T3	(T4,T7) (T5,T8) (T6,T9)
LOW	T1,T7	T2,T8	T3,T9	T4,T5,T6

TOLERANCES UNLESS SPECIFIED

DEC.	INCHES
.X	±.1
.XX	±.01
.XXX	±.005
.XXX	±.0005
ANG	±1/2°



**ELECTRIC MOTORS
GEARMOTORS
AND DRIVES**

TITLE **EXTERNAL WIRING DIAGRAM
3 PHASE W/O PROTECTOR**

MAT'L. **DECAL - 004014**

FINISH

DRAWN ADH 11/06/73

CHK

APPD

SCALE 1=1

REF FIG.2-51

FMF

PREV

11	REDRAWN TO CURRENT STANDARDS	DBT 5/29/97
NO.	REVISION	BY & DATE

CHK	ANG	±1/2°
-----	-----	-------

RFP	04/12/02
DIST	BRF-NLV

CAD FILE	00501001
----------	----------

SIZE	DRAWING NO.	REV.
A	005010-01	11