

INSTALLATION INSTRUCTIONS

SIDE OUTLET KIT

6701

KIT CONTAINS:

- (1) Boot extension—inner
- (1) Boot extension—outer
- (1) Plaster—ground assembly
- (1) Side grille assembly
- (26) Screws #8x3/8 Sheet Metal
- (2) Screws #8x3/4 Sheet Metal
- (3) Side filler strips

STEP 1. Measure and mark wall for vent opening as shown in Fig. A and Fig. B. Check wall for any electrical wiring present before cutting wall opening. Reroute electrical if necessary. Cut hole thru wall both Furnace side and Grille side.

STEP 2. Place plaster-ground in opening from grille side and attach into drywall, as shown in Fig. B

STEP 3. Before setting furnace into position carefully cut 5x7 inch rectangular opening on side of cabinet where embossed. Edges of cut opening must be straight and smooth.

STEP 4. Place outer boot against cabinet and align flanges exactly on edges of cut hole, mark (8) screw locations on cabinet, remove boot and drill #33 size holes for sheet metal screws. Attach outer boot later.

STEP 5. Remove rear knock-out plate as follows:

- A. Punch in lower corners with screwdriver blade.
- B. Break knock-out side and bottom connecting tabs: hold screwdriver blade sideways against tab and strike head of screwdriver lightly with a hammer.
- C. Swing plate outward; bend it back and forth to break the top tabs.

STEP 6. Place inner boot into position, mark and drill as described in step 4.

STEP 7. Secure 1x1 wood backup strip to wall surface next to side outlet as backup for metal filler strips.

STEP 8. Fasten metal filler strips to side of furnace cabinet with front surface opposite across front of wood backup strip. Using metal filler strips as a template drill (12) #33 holes in side of cabinet.

STEP 9. Place furnace in position.

STEP 10. After furnace is placed in position, pass outer boot thru plaster-ground and fasten to cabinet with (8) screws. Place inner boot in position and fasten with (6) screws.

NOTE: Outer and inner boots are sized to extend thru normal plaster thickness of drywall or other thin material, the boots must be trimmed off flush with the wall surface. (grille side).

STEP 11. Place outlet grille in position, align with holes in plaster-ground and fasten with (2) #8 x 3/4 inch sheet metal screws provided.

SEE BACKSIDE FOR FIGURES