




**Shutter/Guard Mount
Exhaust Fans**

AIR CONDITIONING PRODUCTS COMPANY



Manufacturer

QUALITY PRODUCTS FOR AIR MOVEMENT EQUIPMENT

Air Conditioning Products Company

30350 Ecorse Road, Romulus, Michigan 48174

Phone: 734.326.0050 • Fax: 734.326.9632 • www.acpshutters.com

SHUTTER-MOUNT EXHAUST FANS

These easy-to-install, highly efficient exhaust fans have all aluminum improved leakage performance shutters, making them ideal for use in ventilating retail stores, offices, factories, work shops, garages and farm buildings. They are shipped fully assembled with 115 Volt totally enclosed motors and an OSHA-compliant gray polyester powder-coated wire guards. UL and C-UL Listed.

PROPELLER DIA. (IN.)	CFM @ 0.000" SP	CFM @ 0.125" SP	MOTOR RPM	MOTOR HP	SQ. OPENING REQ. (IN.)	ITEM NO.
SPEED CONTROLLABLE						
7	140	--	1550	1/25	8-1/2	SMF 08A
10	585	285	1550	1/25	10-1/2	SMF 10A
12	800	470	1550	1/25	13	SMF 12A
16	1095	720	1550	1/20	17	SMF 16A
18	1860	850	1075	1/15	19	SMF 18A
20	2830	2255	1100	1/4	21	SMF 20D
24	3240	2485	1075	1/4	25	SMF 24C
SINGLE-SPEED						
18	2590	2190	1725	1/4	19	SMF 18B
20	2955	2450	1725	1/4	21	SMF 20C
24	3970	3240	1075	1/3	25	SMF 24D

GUARD-MOUNT EXHAUST FANS

Designed for low-pressure exhausting and cooling applications. Sturdy steel wire guards are OSHA-compliant with a gray polyester powder-coated finish with 4 mounting loops for easy installation. They are shipped fully assembled with 115 Volt totally enclosed motors. UL and C-UL listed.

PROPELLER DIA. (IN.)	CFM @ 0.000" SP	CFM @ 0.125" SP	MOTOR RPM	MOTOR HP	SQ. OPENING REQ. (IN.)	ITEM NO.
7	230	--	1550	1/25	9-5/8	GMF 08A
10	595	405	1550	1/25	11-11/16	GMF 10A
12	820	535	1550	1/25	13-1/2	GMF 12A
16	1060	585	1550	1/20	17-3/8	GMF 16A
18	2515	1780	1725	1/4	20-13/16	GMF 18A
20	2600	1685	1725	1/4	22-3/4	GMF 20A
24	3840	2690	1075	1/3	26-7/8	GMF 24A