

ELKAY[®]

SPECIFICATIONS

Explore Fine Fireclay Undermount Sink Model SWU322010R

GENERAL

Double bowl kitchen sink manufactured from fine fireclay with a durable porcelain glaze. This combination of materials provides a finish that is non-porous and resists staining. Undermount.

DESIGN FEATURES

Bowl Depth: 9-5/8" (244mm) and 7-5/8" (194mm).

Material: Fine fireclay with porcelain glaze. Top of rim is unglazed.

Color Options: Gloss White (WH) or Matte Terra Cotta (TC).


OTHER

Drain Opening: 3-1/2" (89mm).

Note: All Elkay undermount sinks are designed to affix to the underside of any solid surface countertop.

Installation: Support frame under sink (not furnished) is necessary.

Sink complies with ASME A112.19.2-2008/CSA B45.1-08.




Model SWU322010R

SINK DIMENSIONS*

Model Number	Overall				Inside Left Bowl			Inside Right Bowl			Drain Opening	Cutout Countertop	Minimum Cabinet Size
	L	W	D		L	W	D	L	W	D			
SWU322010R	30 ³ / ₄ (781mm)	20 ³ / ₁₆ (513mm)	10 ¹ / ₂ (267mm)	8 ¹ / ₂ (216mm)	16 (406mm)	17 ¹ / ₂ (445mm)	9 ⁵ / ₈ (244mm)	11 ¹ / ₂ (292mm)	15 (381mm)	7 ⁵ / ₈ (194mm)	3 ¹ / ₂ (89mm)	Use sink as Template	36 (914mm)

*Length is left to right. Width is front to back.

Due to the manufacturing process, the sink dimensions are approximate and may vary. No cutout templates available.



SEE OTHER SIDE FOR OPTIONAL ACCESSORIES.

In keeping with our policy of continuing product improvement, Elkay reserves the right to change product specifications without notice. Please visit elkayusa.com for most current version of Elkay product specification sheets.


This specification describes an Elkay product with design, quality and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.

**Explore Fine Fireclay Undermount Sink
Model SWU322010R**

**ELKAY®
SPECIFICATIONS**

OPTIONAL ACCESSORIES*

Model Number	Description	Bowl	Overall			Material/Finish
			L	W	Depth/Thickness	
LK99	Drain	—	Fits 3 1/2" (89mm) Drain Opening			Polished Stainless Steel
LKD35CW	Drain	Both	Fits 3 1/2" (89mm) Drain Opening			Polymer/Cameo White
LKS35CW	Drain	Both	Fits 3 1/2" (89mm) Drain Opening			Polymer/Cameo White
LKSWOBG1618SS	Bottom Grid	Left	15 (381mm)	16 1/8 (410mm)	1 1/4 (32mm)	Polished Stainless Steel
LKSWOBG1215SS	Bottom Grid	Right	10 7/16 (381mm)	13 5/8 (410mm)	1 1/4 (32mm)	Polished Stainless Steel
LKWEOBG1618SS	Bottom Grid	Left	15 (381mm)	16 1/8 (410mm)	1 1/4 (32mm)	Polished Stainless Steel
LKWEOBG1215SS	Bottom Grid	Right	10 7/16 (381mm)	13 5/8 (410mm)	1 1/4 (32mm)	Polished Stainless Steel
LKSWRB1618SS	Rinsing basket with dish rack	Left	15 (381mm)	16 1/8 (410mm)	7 (178mm)	Polished Stainless Steel
LKWUCSS	Utensil Caddy for rinsing basket	—	15 1/8 (384mm)	3 1/2 (89mm)	4 3/8 (111mm)	Polished Stainless Steel



LK99




LKWUCSS




LKD35CW




LKS35CW




LKSWOBG1215SS




LKSWOBG1618SS



LKSWRB1618SS



LKWEOBG1215SS



LKWEOBG1618SS