

# AL652BBI



32" x 23.63" x 23.5" (H x W x D)

Built-in undercounter ADA compliant refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, and black exterior

## Highlights:

32" height for use under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Includes adjustable glass shelves for flexible storage

Zero degree freezer compartment

## Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished black cabinet	Allows the unit to be used freestanding
Reversible door	User-reversible door swing for added flexibility
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Zero degree freezer	Static manual defrost freezer section offers more stability
Adjustable glass shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

**AL652BBI Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.75"
Depth with door at 90°	45.63"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	104.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial

Fan Type	Exterior
Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

