

AL652BBIFR



32" x 23.63" x 23.5" (H x W x D)

Built-in undercounter ADA compliant refrigerator-freezer for general purpose use, w/dual evaporator cooling, SS frame for slide-in panels, and black cabinet

Highlights:

32" height for use under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Zero degree freezer compartment

Improved temperature performance with our unique dual evaporator cooling

Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished black cabinet	Allows the unit to be used freestanding
Stainless steel door frame	Slide a panel into this two-piece U-shaped frame to match your unit to other cabinets (panel size: 23" W x 28" H at up to 1/4" thick)
Professional handle	Stainless steel handle can be reversed with door swing
Reversible door	User-reversible door swing for added flexibility
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators

AL652BBIFR Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	45.63"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	107.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial

Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	2.6 oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

