

CM411LBI7



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide built-in undercounter refrigerator-freezer in white with a lock

Highlights:

ETL-S listed for commercial use

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

Includes a hospital grade cord with a 'green dot' plug

Product Features:

Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability
Reversible door	Keep your options flexible with a reversible door that is easy to switch when your arrangement changes
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

CM411LBI7 Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with Handle	23.0"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	57.0 lbs.
Shipping Weight	80.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	28.75"
Refrigerator - Interior Width	15.75"
Refrigerator - Interior Depth	17.75"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	1.75

High Side PSI	205.0
Low Side PSI	103.0
Level Legs	2
Wheels	2

