

CM411LBI7IFADA



32" x 19.25" x 21.38" (H x W x D)

Commercially listed ADA compliant 20" wide built-in refrigerator-freezer with a lock, white exterior, and integrated door frame for overlay panels

Highlights:

ETL-S listed for commercial use

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Commercially listed	ETL-S listed to NSF standards for commercial use
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Integrated door frame	Stainless steel door frame accepts overlay panels for users to create a custom look over the front (panel size: 19 1/2" W x 31 1/2" H and at least 3/4" thick)
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability

CM411LBI7IFADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Manual
Door	Panel-Ready
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	28.75"
Refrigerator - Interior Width	15.75"
Refrigerator - Interior Depth	17.75"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75 oz.
High Side PSI	205.0

Low Side PSI
Level Legs
Wheels

