

# CM421BL7SSH



33.5" x 19.25" x 21.38" (H x W x D)

Commercially listed 20" wide counter height refrigerator-freezer with a lock, stainless steel door, horizontal handle and black cabinet

## Highlights:

ETL-S listed for commercial use

Slim 20" width is ideal for any setting

Factory installed lock provides security you can count on

Professional look with a durable stainless steel wrapped door and sleek horizontal handle

## Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Commercially listed	ETL-S listed to NSF standards for commercial use
Fully finished black cabinet	Allows the unit to be used freestanding
Stainless steel wrapped door	Durable 304 grade wrapping
Professional horizontal handle	Thin 14mm diameter on stainless steel handle, mounted horizontally on the door
Factory installed lock	Top-mounted for convenient security
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Manual defrost	Efficient performance with reliable temperature stability
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

**CM421BL7SSH Specifications:**

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Manual
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	28.75"
Refrigerator - Interior Width	15.75"
Refrigerator - Interior Depth	17.75"
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	1.75
High Side PSI	205.0

Low Side PSI

Level Legs

Wheels

