

CM421BLBISSTB



33.5" x 19.25" x 21.38" (H x W x D)

20" wide built-in refrigerator-freezer with a lock, stainless steel door, towel bar handle and black cabinet

Highlights:

Flexible design allows built-in or freestanding use in 20" wide spaces

Factory installed lock provides security you can count on

Professional style with 304 grade stainless steel wrapped door and curved towel bar handle

Jet black cabinet with adjustable glass shelves included

Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished black cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Stainless steel wrapped door	Durable 304 grade wrapping
Professional towel bar handle	A curved stainless steel handle provides generous room for a comfortable grip
Manual defrost	Efficient performance with reliable temperature stability
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in a bottom crisper

CM421BLBISSTB Specifications:

Overview	
Height	33.5"
Height to Hinge Cap	34.0"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Manual
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	28.75"
Refrigerator - Interior Width	15.75"
Refrigerator - Interior Depth	17.75"
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0

Level Legs

Wheels

