

# CT66BBIIFADA



32" x 23.63" x 23.5" (H x W x D)

Built-in undercounter ADA compliant refrigerator-freezer for general purpose use, cycle defrost w/dual evaporator cooling, panel-ready door, and black cabinet

### Highlights:

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" wide spaces

Improved temperature performance with our unique dual evaporator cooling

Zero degree freezer compartment

### Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished black cabinet	Allows the unit to be used freestanding
Integrated door frame	Stainless steel door frame accepts full overlay panels to match adjacent cabinetry (panel size: 23 5/16" W x 28 1/4" H and at least 3/4" thick)
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Zero degree freezer	Static manual defrost freezer section offers more stability
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Door storage	Store tall bottles and condiments right on the door for convenient access

**CT66BBIFADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with door at 90°	45.13"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	100.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial

Refrigerant Type	R134a
Refrigerant Amount	2.6 oz.
High Side PSI	285.0
Low Side PSI	70.0
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

