

CT66JBISSHV



33.25" x 23.63" x 23.5" (H x W x D)

Built-in undercounter refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, SS door, thin handle and white cabinet

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel door complete with sleek handle adds modern elegance to any setting

Improved temperature performance with our unique dual evaporator cooling

Zero degree freezer compartment

Product Features:

Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel door	Durable design with lasting elegance
Professional stainless steel handle	Thin 14mm diameter on stainless steel handle, mounted vertically for a sleek look
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator cooling	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Zero degree freezer	Static manual defrost freezer section offers more stability
Adjustable shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup

CT66JBISHV Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	34.75"
Width	23.63"
Depth	23.5"
Depth with Handle	25.63"
Depth with door at 90°	45.63"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	148.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years

Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Wire
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes

Thermostat Type	Dial
Fan Type	Exterior
Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

