

CT66JSSH



33.25" x 23.63" x 23.5" (H x W x D)

Freestanding refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, SS door, horizontal handle and white cabinet

Highlights:

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Stainless steel wrapped door includes horizontal handle for a professional look

Improved temperature performance with our unique dual evaporator cooling

Zero degree freezer compartment

Product Features:

Slim counter height dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Stainless steel door	Durable design with lasting elegance
Professional horizontal handle	Thin 14mm diameter on stainless steel handle set horizontally across the door
Fully finished white cabinet	Allows the unit to be used freestanding
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Zero degree freezer	Static manual defrost freezer section offers more stability
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Clear crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer

CT66JSSH Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.25"
Depth with door at 90°	45.0"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial

Fan Type	Exterior
Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

