

FF511LSSHVADA



32" x 19.25" x 21.38" (H x W x D)

ADA Compliant 20" wide counter height all-refrigerator, auto defrost with a lock, stainless steel door, thin handle, and white cabinet

Highlights:

32" height for use in ADA compliant settings

Freestanding all-refrigerator offers full 4.1 cu.ft. capacity in slim 20" width

Factory installed lock provides security you can count on

Save time and energy with low maintenance automatic defrost

Product Features:

ADA compliant	32" high meets ADA guidelines
Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Fully finished white cabinet	Allows the unit to be used freestanding
Factory installed lock	Top-mounted for convenient security
Stainless steel wrapped door	Durable 304 grade wrapping
Professional handle	Thin 14mm diameter on stainless steel handle
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in a bottom crisper

FF511LSSHVADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.5"
Width	19.25"
Depth	21.38"
Depth with door at 90°	39.5"
Capacity	4.1 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	406.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs.
Shipping Weight	85.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.75
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5"
Interior Width	15.75"

Interior Depth	18.0"
Compressor Step Height	8.0"
Compressor Step Width	17.0"
Compressor Step Depth	6.75"

