



FF61BIDPL



33.5" x 23.63" x 23" (H x W x D)

Built-in undercounter all-refrigerator for residential use, auto defrost with a diamond plate door, towel bar handle, and white cabinet

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Textured diamond plate door in aluminum with polished towel bar handle offers an industrial look

Automatic defrost ensures minimum user maintenance

Deluxe interior includes a scalloped wine shelf

Product Features:

Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Slim undercounter dimensions	Ideal 24" footprint offers full 5.5 cu.ft. storage capacity in a slim fit
Diamond plate door	Textured diamond plate finish in wrapped aluminum creates a unique industrial look
Automatic defrost	Reduced user maintenance with automatic defrost operation
Professional towel bar handle	Curved handle in polished stainless steel completes the look
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Fruit and vegetable crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer
Door storage	Keep tall bottles and condiments right on the door for convenient access
Wine shelf	Removable scalloped wine shelf is included to store champagne and wine bottles



FF61BIDPL Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.0"
Depth with door at 90°	45.38"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Diamond Plate
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	307.0kWh/year
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Wine Bottle Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.7
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	

Interior Height	26.25"
Interior Width	21.0"
Interior Depth	18.0"
Compressor Step Height	5.5"
Compressor Step Width	21.0"
Compressor Step Depth	6.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com www.summitappliance.com