



FF61BIIF



33.5" x 23.63" x 23" (H x W x D)

Built-in undercounter auto defrost all-refrigerator for residential use with a customizable door front to accept overlay panels and white cabinet finish

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Door accepts overlay panels for a custom look that can seamlessly blend into your kitchen cabinetry

Automatic defrost ensures minimum user maintenance

Includes adjustable glass shelves for spill-proof storage

Product Features:

Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Integrated door frame	Customize the front by mounting an overlay panel over the door; seamless look can blend into other cabinetry with no exposed frame. Handle not included (panel size: 23 5/16" W x 28 1/4" H and at least 3/4" thick)
Automatic defrost	Reduced user maintenance with automatic defrost operation
Adjustable glass shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Fruit and vegetable crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer
Door shelves	Keep tall bottles and condiments right on the door for convenient access
Wine shelf	Removable scalloped wine shelf is included to store champagne and wine bottles
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior





FF61BIIF Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.0"
Depth with door at 90°	45.38"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	307.0kWh/year
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Wine Bottle Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.7oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	

Interior Height	26.25"
Interior Width	21.0"
Interior Depth	18.0"
Compressor Step Height	5.5"
Compressor Step Width	21.0"
Compressor Step Depth	6.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com