



# FF61CSS



33.25" x 23.75" x 23" (H x W x D)

Built-in undercounter all-refrigerator for residential use, auto defrost with complete stainless steel exterior

### Highlights:

Fully wrapped stainless steel cabinet and door bring true luxury under the counter

Flexible design allows built-in or freestanding use in 24" spaces

Automatic defrost ensures minimum user maintenance

Includes adjustable glass shelves for spill-proof storage

### Product Features:

Slim undercounter dimensions	Our unique 24" wide models offer full capacity in a slim fit
Complete stainless steel cabinet and door	Durable construction with modern style
Automatic defrost	Reduced user maintenance with automatic defrost operation
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished cabinet	Allows the refrigerator to be used as a freestanding model
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Fruit and vegetable crisper	Get the longest life and best taste out of produce by storing it in a convenient slide drawer
Wine shelf	Removable scalloped wine shelf is included to store champagne and wine bottles



## FF61CSS Specifications:

Overview	
Height	33.25"
Width	23.75"
Depth	23.0"
Depth with Handle	25.25"
Depth with door at 90°	45.38"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	307.0kWh/year
Amps	1.0
Weight	110.0 lbs.
Shipping Weight	140.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Wine Bottle Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.7oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	

Interior Height	26.25"
Interior Width	21.0"
Interior Depth	18.0"
Compressor Step Height	5.5"
Compressor Step Width	21.0"
Compressor Step Depth	6.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com