

# FF6BADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant all-refrigerator for freestanding general purpose use, with automatic defrost operation and black exterior

### Highlights:

32" height for use in ADA compliant settings

Includes adjustable glass shelves for flexible storage

Automatic defrost ensures minimum user maintenance

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

### Product Features:

ADA compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Slim counter height dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Fully finished black cabinet	Allows the unit to be used freestanding
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer
Door storage	Keep tall bottles and condiments right on the door for easy access

**FF6BADA Specifications:**

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	102.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"

Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

