

FF6BDPL



33.25" x 23.63" x 23.63" (H x W x D)

Freestanding counter height all-refrigerator for general purpose use, auto defrost w/diamond plate wrapped door, towel bar handle, and black cabinet

Highlights:

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Includes adjustable glass shelves for flexible storage

Textured diamond plate door in aluminum with polished towel bar handle offers an industrial look

Automatic defrost ensures minimum user maintenance

Product Features:

Slim counter height dimensions	Ideal 24" footprint offers full 5.5 cu.ft. storage capacity in a slim fit
Automatic defrost	Reduced maintenance with auto defrost system
Fully finished black cabinet	Allows the unit to be used freestanding
Professional towel bar handle	Curved handle in polished stainless steel completes the look
Diamond plate door	Textured aluminum finish offers an industrial look
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Door storage	Store tall bottles and condiments right on the door for convenient access

FF6BDPL Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.25"
Width	23.63"
Depth	23.63"
Depth with Handle	25.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Diamond Plate
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"

Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

